




无锡市 中谊药化机械有限公司
Wuxi Zhongyi Chemical Pharmaceutical Machinery Equipment Co.Ltd

RJWJ-15 Paintball Production Line



无锡市 中谊药化机械有限公司

Wuxi zhongyi chemical pharmaceutical machinery equipment Co., Ltd

Tell: 0086-510-85180156

Fax: 0086-510-85185238

www.wxzoyi.com



Movable Gelatin Melting Tank

RJWJ-RJ series Movable Gelatin Melting Tank is special equipment for gelatin melting, mixing, material preparation and vacuumizing and so on during small production of paintball.



Technical Parameter	
Model	RJWJ-RJ100
Volume	100L
Vacuum degree	<0.09mpa
Working temperature	0-100°C
Mixing Rotational speed	33-50rpm
Motor power	3 kw
Dimension	φ750x1300mm
Weight	70kg

Water Cycle Vacuum Pump



Technical Parameter	
Motor power	1.1kw



RJWJ-15 Paintball Machine

RJWJ-15 Paintball Machine is improved according to the features of paintball production and on the basis of the softgel encapsulation machine. This machine is suitable for the research and production of paintball and bath balls. This machine is the best style for the small production of paintballs and bath balls it has suitable performance, lower cost, precise volume and high degree of automation. The liquid level of the gelatin box is controlled by the level sensor and the injector adopts new temperature controlling system, so the temperature is stable and can be controlled precisely. The touch screen is designed reasonable and it is easy to learn and operate. The maximum capacity of this machine is about 10,800 balls/h.



Technical Parameter	
Die roller speed	0-5 RPM
Die roller size	φ103x100mm
Die roller Pressure	0.1-0.5Mpa
Capacity	10,800 balls/h, 0.68"
Power	380V50Hz
Motor power	0.75kw
Total power	5kw
Volume precision	≥±1%
Dimension	1680x600x1550(h)mm
Weight	550kg



SS Shaping and Drying Tumbler

Stainless steel tumbler is used for shaping and drying the paintballs. Each tumbler equips one fan, each rotary basket can be individually positive and negative rotation, frequency control, speed adjustable, its control can be used as the shaping when the host computer is connected by PLC automatic control, can also be controlled manually in the pre-dry separate operation. When used for shaping, the water content of the paintball piece which are newly pressed can be reduced from 45% to 35%.



Technical Parameter	
Model	ZL15
The number of tumbler	2 sections
Rotate speed	13 r/min
Motor power	90Wx2
Fan air flow	1200m ³ /h(one basket)
Fan speed	1250r/min
Tumbler size	φ450x615mm
Dimension	1200x520x1000mm
Weight	150kg